

Product data sheet

Specifications



3HP230VATV61w/ lonworksandconduitbox

ATV61HU22M3T1LW

⚠ Discontinued on: Dec 31, 2017

⚠ End-of-service on: Oct 11, 2022

⚠ Discontinued

Main

Asynchronous Motor Control Profile	Variable torque standard
Device Short Name	ATV61
Range Of Product	Altivar 61

Complementary

[In] Rated Current	11 A 8 A 1 phase
Cable Entry	Type 1 conduit entry outdoor
Communication Port Protocol	LonWorks CANopen Modbus
Input Voltage	208/240 V AC
Keypad Type	LCD keypad
Motor Power Hp	3 hp 2 hp, 1 phase
Motor Power Kw	2.2 kW 1.5 kW, 1 phase
Network Number Of Phases	3 phases output 1 phase input 3 phases
Output Voltage	<= rated supply voltage

Environment

Emc Filter	Class A EMC filter integrated
Ip Degree Of Protection	IP20
Nema Degree Of Protection	No enclosure rating (open device)
Protective Treatment	None

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications