



Main

Asynchronous motor control profile	Variable torque standard
Device short name	ATV61
Range of product	Altivar 61

Complementary

[In] rated current	5.8 A
Cable entry	Type 1 conduit entry outdoor
Communication port protocol	CANopen LonWorks Modbus
Input voltage	400/480 V AC
Keypad type	LCD keypad
Motor power hp	3 hp
Motor power kW	2.2 kW
Network number of phases	3 phases output
Output voltage	<= rated supply voltage

Environment

EMC filter	Class A EMC filter integrated
IP degree of protection	IP20
NEMA degree of protection	No enclosure rating (open device)
Protective treatment	None