

Product data sheet

Specifications



SPEEDDRIVE,1HP,230V,ATV71+ conduit box

ATV71H075M3T1

 **Discontinued on:** Jan 27, 2022

 **Discontinued**

Main

Asynchronous Motor Control Profile	Constant torque standard
Device Short Name	ATV71
Range Of Product	Altivar 71

Complementary

[In] Rated Current	4.8 A 3 A 1 phase
Cable Entry	Type 1 conduit entry outdoor
Communication Port Protocol	CANopen Modbus
Input Voltage	208/240 V AC
Keypad Type	LCD keypad
Motor Power Hp	1 hp 0.5 hp, 1 phase
Motor Power Kw	0.75 kW 0.37 kW, 1 phase
Network Number Of Phases	3 phases output 1 phase input 3 phases
Output Voltage	<= rated supply voltage

Environment

Emc Filter	Class A EMC filter integrated
Ip Degree Of Protection	IP20
Nema Degree Of Protection	No enclosure rating (open device)
Protective Treatment	None

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications