

Product data sheet

Specifications



SPEEDDRIVE200HP460VATV71+CONDUIT BOX

ATV71HC13N4T1

 **Discontinued on:** Jan 27, 2022

 **Discontinued**

Main

Asynchronous Motor Control Profile	Constant torque standard
Device Short Name	ATV71
Range Of Product	Altivar 71

Complementary

[In] Rated Current	259 A
Cable Entry	Type 1 conduit entry outdoor
Communication Port Protocol	Modbus CANopen
Impregnation Material	Conformal coated
Input Voltage	400/480 V AC
Keypad Type	LCD keypad
Motor Power Hp	200 hp
Motor Power Kw	130 kW
Network Number Of Phases	3 phases output 1 phase input
Output Voltage	<= rated supply voltage

Environment

Emc Filter	Class A EMC filter integrated
Ip Degree Of Protection	IP20
Nema Degree Of Protection	No enclosure rating (open device)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications