

Product data sheet

Specifications



SPEEDDRIVE,25HP,460V,ATV71 + conduit box

ATV71HD18N4T1

 **Discontinued on:** Jan 27, 2022

 **Discontinued**

Main

Asynchronous Motor Control Profile	Constant torque standard
Device Short Name	ATV71
Range Of Product	Altivar 71

Complementary

[In] Rated Current	41 A
Cable Entry	Type 1 conduit entry outdoor
Communication Port Protocol	Modbus CANopen
Input Voltage	400/480 V AC
Keypad Type	LCD keypad
Motor Power Hp	25 hp
Motor Power Kw	18 kW
Network Number Of Phases	3 phases output 1 phase input
Output Voltage	<= rated supply voltage

Environment

Emc Filter	Class A EMC filter integrated
Ip Degree Of Protection	IP20
Nema Degree Of Protection	No enclosure rating (open device)
Protective Treatment	None

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications