

Product data sheet

Specifications



heavy duty PowerLogic PFC Capacitor, 30.3/0 kvar - 440 V - 50/60Hz

BLRCH303A000B44

Main

Range Of Product	PowerLogic
Product Or Component Type	Heavy duty capacitor
Network Frequency	50/60 Hz
Series Name	HDuty
Network Harmonic Content	<= 20 %
Electrical Parameters	30.3 kvar 50 Hz
Maximum Permissible Voltage	1.1 x Un (8 hours over 24 hours)
Continuous Overcurrent Capacity	1.8 x In
Rated Voltage	440 V AC 50/60 Hz

Complementary

Dielectric Losses	< 0.2 W/kvar
Power Losses	< 0.5 W/kVAr
Capacitance Tolerance	- 5 % to 10 %
Voltage Test	2.15 x Un AC between terminals for 10 s <= 660 V - 3 kV AC between terminal and container for 10 s >= 660 V - 6 kV AC between terminal and container for 10 s
Inrush Current	250 x In
Maximum Switching Operation Per Year	7000
Service Life In Hours	130000 h
Dielectric Material	Metallized polypropylene film with Zn/Al alloy, special resistivity & profile, special edge (wave cut)
Impregnation Material	Non-PCB dry PUR resin Biodegradable
Type Of Installation	Indoor installation
Connections - Terminals	ClampTite terminal
Mounting Mode	Upright/horizontal
Diameter	136 mm
Height	242 mm
Net Weight	3.2 kg

Environment

Standards	IEC 60831-2 IEC 60831-1
-----------	----------------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP20
Operating Altitude	2000 m
Temperature Class	D
Ambient Air Temperature For Operation	-25...55 °C
Relative Humidity	95 %

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	19 cm
Package 1 Width	18.5 cm
Package 1 Length	31.5 cm
Package 1 Weight	3.814 kg
Unit Type Of Package 2	S06
Number Of Units In Package 2	15
Package 2 Height	74 cm
Package 2 Width	60 cm
Package 2 Length	80 cm
Package 2 Weight	57.21 kg
Unit Type Of Package 3	S06
Number Of Units In Package 3	15
Package 3 Height	74 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	57.21 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins