



Main

Product or component type	Uninterruptible power supply (UPS)
Mounting support	Wall-mount

Complementary

Display type	LED indicator
Type of signal	Sine wave
Network frequency	50...60 Hz
Power range	500 VA
Electrical connection	Output: 4 outlet Australian Input: 1 cable
Local signalling	Alarm, distinctive for low battery Alarm, continuous or intermittent tone for overload LCD display for status and alert
Cable length	1.52 m
Battery type	Lead-acid battery Sealed rechargable Internal battery
Charging time	8 h

Environment

Relative humidity	0...90 %, non-condensing
Operating altitude	0...1968.3 m
Ambient air temperature for operation	0...40 °C
Product certifications	CE RCM

Contractual warranty

Warranty	2 years
----------	---------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications