



Main

Product or component type	Uninterruptible power supply (UPS)
Mounting support	Wall Floor
Reset	Automatic reset
Topology	Line interactive

Complementary

Type of installation	Indoor
Surge Energy	156 J
Type of signal	Stepped approximation to a sinewave
Protection device type	Surge protection device (SPD) Miniature circuit breaker (MCB)
Protection type	Fuse protection
Input voltage	230 V AC
Output voltage	230 V AC
IP degree of protection	IP20
Transfer time	6 ms
Network frequency	45...65 Hz
Power range	800 VA 450 W
Electrical connection	Input: 1 inlet Schuko CEE 7/P Output: 4 outlet Schuko CEE 7
Local signalling	Alarm, distinctive for low battery Alarm, continuous or intermittent tone for overload LED for battery status
Battery type	Lead-acid battery
Number of batteries	1
Charging time	8 h
Battery voltage	12 V
Battery life	5 year(s)
Quantity per set	Set of 1
Net weight	5.3 kg
Height	92.5 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	160.5 mm
Depth	305 mm

Environment

Acoustic level	< 40 dBA
Relative humidity	0...90 %, non-condensing
Operating altitude	0...6561 ft
Ambient air temperature for operation	0...40 °C
Product certifications	CE

Contractual warranty

Warranty	2 years
----------	---------
