

# Product data sheet

Specifications



## Odace/Unica Wireless - mobile socket-outlet relay - 2P+E, DE - 230 VAC - white

CCT1A020

⚠ Discontinued on: Apr 15, 2021

⚠ Discontinued

### Main

Range Compatibility	IHC Odace Wireless Unica Wireless Alvais RF Free RF
Product Or Component Type	Mobile socket-outlet relay
Transmission Frequency	868.3 MHz
Outlet Poles Configuration	2P + E
Outlet Standard	German
Outlet Standard Description	Side earth
[Ue] Rated Operational Voltage	230 V AC +/- 10 % at 50 Hz
Provided Equipment	One key for local control
Colour Tint	White

### Complementary

Operating Distance	10...50 m indoor <= 300 m outdoor
Load Type	230 V AC compact fluorescent lamp - 1840 VA 230 V AC fan - 1380 W 230 V AC halogen lamp - 2300 W 230 V AC incandescent lamp - 2300 W 230 V AC LED lamp - 1840 W Fluorescent tube (diameter: 28...38 mm): 1 1-10 V dimmable electronic ballast - 1840 VA Low voltage halogen lamp with ferromagnetic transformer - 1840 VA Low voltage halogen lamps with toroidal transformer - 1840 VA Motor - 1380 W
Standards	IEC 61000-6-3 EN 60669-2-1 ETSI EN 300 220 73/23/EEC ETSI EN 301 489 99/5/EEC 89/336/EEC EN 60669-1 IEC 61000-6-2
Ambient Air Temperature For Operation	-5...50 °C
Relative Humidity	20...95 %
Height	111 mm
Width	51 mm
Depth	73 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Ip Degree Of Protection	IP20
Environmental Characteristic	Petrol Acetone Alcohol UV resistant Bleach Oil Window-cleaning fluid Liquid soap

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6 cm
Package 1 Width	12 cm
Package 1 Length	12.2 cm
Package 1 Weight	243 g

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>