



Complementary

Range of product	ARGUS standard movement detector
Range	ARGUS
Product or component type	Presence detector with IR receiver
Colour tint	White
Network frequency	50/60 Hz
Input function	Switch
Output voltage	220...250 V
Communication port protocol	DALI
Number of channels	2
Control type	Movement sensor
Function available	Master function Switching, toggling, dimming
Light intensity adjustment	10...2000 lux 25...2000 lux
Horizontal detection angle	360 °
Detection face	Radius: 4000 mm
Device mounting	Flush Surface
Mounting height	2.5 m

Environment

IP degree of protection	IP40 IP42
-------------------------	--------------

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1611 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
Product environmental profile	Available
Product end of life instructions	Available