



Complementary

Range of product	ARGUS standard movement detector
Range	ARGUS
Product or component type	Movement detector
Load type	Halogen lamp: 1000 W AC Incandescent lamp: 1000 W AC Compact fluorescent lamp: 3 x 23 W AC Fluorescent tube: 200 VA AC Capacitive: : 6 A 21 µF AC Capacitive: : 10 A 14 µF AC Low voltage halogen lamp with wire-wound transformer: 500 VA Low voltage halogen lamp with electronic transformer: 250 VA
Colour tint	White
Type of packing	Carton
[Ue] rated operational voltage	220...240 V
Network frequency	50 Hz
[Ue] rated operational voltage	220...240 V
Output current	10 A
Type of setting	Time adjustment Light sensitivity adjustable
Time delay	5 s...10 min
Light intensity adjustment	5...2000 lux
Horizontal detection angle	0...360 °
Detection face	Radius: 3.9 m
Condition of use	Indoor use only
Material	ABS + PC matt
Device mounting	Ceiling
Mounting height	3 m

Environment

IP degree of protection	IP20
-------------------------	------

Environmental health and issues	Halogen free
---------------------------------	--------------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1342 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------
