



### Complementary

Range of product	ARGUS standard movement detector
Range	ARGUS
Product or component type	Movement detector
Load type	Incandescent lamp: 1000 W AC Fluorescent tube: 250 VA AC Compact fluorescent lamp: 4 x 23 W AC Capacitive: : 6 A 28 µF AC Capacitive: : 10 A 21 µF AC Halogen lamp: 800 W AC Low voltage halogen lamp with wire-wound transformer: 500 VA Low voltage halogen lamp with electronic transformer: 315 VA
Colour tint	White
Type of packing	Carton
[Ue] rated operational voltage	220...240 V
Network frequency	50 Hz
[Ue] rated operational voltage	220...240 V
Output current	10 A
Type of setting	Time adjustment Light sensitivity adjustable
Time delay	5 s...20 min
Light intensity adjustment	5...2000 lux
Horizontal detection angle	0...360 °
Detection face	Frontal: 12 m
Material	PC (polycarbonate) matt
Device mounting	Surface
Mounting height	2.5 m

### Environment

IP degree of protection	IP55
Ambient air temperature for operation	-15...40 °C
Environmental health and issues	Halogen free

Market segment	Small commercial Residential
----------------	---------------------------------

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0903 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Available <a href="#">End of Life Information</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------