



### Overview

Model Name	PowerShield 27W DC UPS, 13V Out, Floating, 3-Conductor Schuko Pwr Cord
Includes	User Manual
Standard Lead Time	Special Order - Call for Quoted Lead Times
Product Distribution	Albania , Algeria , Andorra , Angola , Armenia , Austria , Azerbaijan , Bahrain , Belarus , Belgium , Benin , Bosnia And Herzegovina , Botswana , Bulgaria , Burkina Faso , Burundi , Cameroon , Central African Republic , Chad , Congo , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Cote D'Ivoire , Croatia , Cyprus , Czech Republic , Denmark , Djibouti , Egypt , Equatorial Guinea , Eritrea , Estonia , Ethiopia , Finland , France , Gabon , Gambia , Georgia , Germany , Ghana , Gibraltar , Greece , Guadeloupe , Guinea , French Guiana , Hungary , Iceland , Iran (Islamic Republic Of) , Iraq , Ireland , Israel , Italy , Jordan , Kazakhstan , Kenya , Kuwait , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Madagascar , Malawi , Mali , Malta , Martinique , Mauritania , Mauritius , Mayotte , Moldova, Republic Of , Mongolia , Morocco , Mozambique , Namibia , Netherlands , Niger , Nigeria , Norway , Oman , Pakistan , Poland , Portugal , Reunion , Romania , Russian Federation , Rwanda , Saudi Arabia , Senegal , Sierra Leone , Slovakia (Slovak Republic) , Slovenia , Somalia , South Africa , Spain , Sudan , Suriname , Sweden , Switzerland , Tajikistan , TANZANIA, UNITED REPUBLIC OF , Togo , Tunisia , Turkey , Turkmenistan , Uganda , Ukraine , United Arab Emirates , Uzbekistan , Western Sahara , Yemen , Zambia , Zimbabwe

### Communications & Management

Audible Alarm	Alarm when on battery : distinctive low battery alarm
---------------	---

### Output

Output Voltages	12
Output Power Capacity	27 Watts / 27 VA
Max Configurable Power (Watts)	27 Watts / 27 VA

### Input

Input Frequency	47 - 70 Hz (auto sensing)
Input Connections	IEC 320 C5
Cord Length	2 meters
Input voltage range for main operations	87 - 264 V
Input Voltages	100 - 240
Number of Power Cords	1

## Physical

Maximum Height	190.0 mm
Maximum Width	241.0 mm
Maximum Depth	76.0 mm
Net Weight	3.41 kg
Shipping Weight	4.09 kg
Shipping Height	343.0 mm
Shipping Width	343.0 mm
Shipping Depth	114.0 mm
Color	Beige
Units per Pallet	90.0

## Environmental

Operating Environment	-20 - 50 °C
Operating Relative Humidity	5 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-20 - 50 °C
Storage Relative Humidity	5 - 95 %
Storage Elevation	0-15000 meters

## Conformance

Approvals	C-tick , CE , EN 55022 Class B , EN 60950 , EN 61000-3-2 , FCC Part 15 Class B , IEC 60950 , UL 60950 , UL Listed , cUL Listed
Standard warranty	2 years repair or replace

## Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs