

# Product data sheet

Specifications



## Stago - cover - 100 mm - L=2 m - steel - pre-galvanized - RAL1023

CSU0816113FS123

⚠ Discontinued on: Jan 3, 2022

⚠ Discontinued

### Main

Range Of Product	Stago
Product Or Component Type	Cover
Mounting Location	Partly outdoor environment with low exposure to corrosion white space - data center

### Complementary

Product Destination	Cable duct
Fixing Mode	By clamp
Material With Surface Treatment	Steel pre-galvanized, RAL 1023
Corrosion Class	C2
Length	2000 mm
Height	11 mm
Width	100 mm

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1 cm
Package 1 Width	10 cm
Package 1 Length	200 cm
Package 1 Weight	2 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations