



Main

Range of product	Stago
Product or component type	Cable tray
Cable support type	Knock-out holes
Mounting location	For partly outdoor environment with low exposure to corrosion, such as ware-houses and parking garages

Complementary

Product destination	KG281 cable tray
Fixing mode	Screwless
Material with surface treatment	Steel, pre-galvanized
Corrosion class	C2
Thickness	0.8 mm
Perforation location	Side perforation
Nominal cross section	7200 mm ²
Height	60 mm
Width	120 mm
Length	3000 mm
Product weight	1.608 kg / 100 m

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications