



Main

Range of product	Stago
Range	Stago
Product or component type	Bend
Device application	Cable management

Complementary

Operating angle	90 °
Direction change type	Horizontal
Inner radius	100 mm
Adjustment	Fixed
Product destination	KG281 cable tray 60 mm height and 70 mm width
Fixing mode	By screw
Shape	Bended
Material with surface treatment	Stainless steel, pre-galvanized (RAL 1013)
Corrosion class	C2
Thickness	1 mm
Height	64 mm
Width	273 mm
Depth	273 mm
Product weight	0.631 kg / set of 1

Environment

Mounting location	For partly outdoor environment with low exposure to corrosion, such as ware-houses and parking garages
-------------------	--

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1101 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations