


Product data sheet

Specifications



Stago - vertical t-piece formed 60x120mm pre-galvanized RAL1013

CSU08702019

 **Discontinued on:** Jan 3, 2022

 **Discontinued**

Main

Product Or Component Type	T-piece
---------------------------	---------

Complementary

Operating Angle	90 °
Direction Change Type	Vertical
Adjustment	Fixed
Product Destination	Cable tray KG281 H= 60 mm W= 120 mm
Fixing Mode	By screw
Material	Steel pre-galvanized, RAL 1013
Inner Radius	120 mm
Height	263 mm
Width	123 mm
Depth	503 mm

Environment

Atmospheric-Corrosivity Category	C2
Environmental Characteristic	Partly outdoor environment with low exposure to corrosion ware-houses and parking garages
Net Weight	1.687 kg / set of 1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications