


Product data sheet

Specifications



Stago - cover for 90° Bend - 300 mm - sheet steel - pre-galvanized

CSU3006302FS123

 **Discontinued on:** Mar 21, 2017

 **Discontinued**

Main

| | |
|---------------------------|---|
| Range Of Product | Stago |
| Product Or Component Type | Cover |
| Mounting Location | Partly outdoor environment with low exposure to corrosion ware-houses and parking garages |

Complementary

| | |
|---------------------------------|--------------------------------------|
| Operating Angle | 90 ° |
| Direction Change Type | Horizontal |
| Product Destination | Bend for cable tray 300 mm width |
| Fixing Mode | Snap-on |
| Material With Surface Treatment | Sheet steel pre-galvanized, RAL 1023 |
| Height | 11 mm |
| Width | 300 mm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications