


Product data sheet

Specifications



Stago - cover horizontal bend 90° flat 330mm pre-galvanized oyster white RAL1013

CSU30063312

⚠ Discontinued on: Sep 30, 2020

⚠ End-of-service on: Oct 26, 2020

⚠ Discontinued

Main

Range	Stago
Product Or Component Type	Cover
Mounting Location	Partly outdoor environment with low exposure to corrosion ware-houses and parking garages

Complementary

Operating Angle	90 °
Direction Change Type	Horizontal
Product Destination	Bend KG281 for cable tray 35 mm 330 mm width Bend KG281 for cable tray 60 mm 330 mm width Bend KG281 for cable tray 85 mm 330 mm width Bend KG281 for cable tray 110 mm 330 mm width
Fixing Mode	Screwless
Material With Surface Treatment	Steel pre-galvanized, RAL 1013
Colour Tint	Oyster white (RAL 1013)
Corrosion Class	C2
Length	430 mm
Height	11 mm
Width	430 mm
Net Weight	1.223 kg / set of 1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications