


Product data sheet

Specifications



Stago - cover horizontal bend 90° flat 500mm 1.5mm hot-dip galvanized

CSU300650126

⚠ Discontinued on: Jan 3, 2022

⚠ Discontinued

Important message: This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link www.wibe-group.com for further details.

Main

Range	Stago
Product Or Component Type	Cover
Mounting Location	Area with high level of environmental corrosion, humidity and airborne pollution industrial and coastal areas, chemical plants

Complementary

Operating Angle	90 °
Direction Change Type	Horizontal
Product Destination	Bend TV184 for cable tray 35 mm 500 mm width Bend TV184 for cable tray 60 mm 500 mm width Bend TV184 for cable tray 85 mm 500 mm width Bend TV184 for cable tray 110 mm 500 mm width
Fixing Mode	Screwless
Material With Surface Treatment	Steel hot-dip galvanized
Corrosion Class	C3/C4
Length	598 mm
Height	11 mm
Width	598 mm
Net Weight	4.816 kg / set of 1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1 cm
Package 1 Width	60 cm
Package 1 Length	60 cm
Package 1 Weight	5 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations