

Product data sheet

Specifications



Stago - cover t piece flat - 70 mm - steel - pre-galvanized - RAL1013

CSU30150712

⚠ Discontinued on: Sep 30, 2020

⚠ End-of-service on: Oct 26, 2020

⚠ Discontinued

Main

Range Of Product	Stago
Product Or Component Type	Cover
Mounting Location	Partly outdoor environment with low exposure to corrosion ware-houses and parking garages

Complementary

Operating Angle	90 °
Direction Change Type	Horizontal
Product Destination	T-piece KG281 for cable tray 60 mm 70 mm width
Fixing Mode	Screwless
Material With Surface Treatment	Steel pre-galvanized, RAL 9016
Corrosion Class	C2
Length	170 mm
Height	11 mm
Width	270 mm
Net Weight	0.26 kg / set of 100

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications