



Main

Range of product	Stago
Product or component type	Cover
Mounting location	For partly outdoor environment with low exposure to corrosion, such as ware-houses and parking garages

Complementary

Operating angle	90 °
Direction change type	Horizontal
Product destination	T-piece for KG281 cable tray 60 mm height and 200 mm width
Fixing mode	Screwless
Material with surface treatment	Steel, pre-galvanized (RAL 9016)
Corrosion class	C2
Product weight	0.748 kg / set of 100