



Main

Range of product	Stago
Product or component type	Cover
Mounting location	For partly outdoor environment with low exposure to corrosion, such as ware-houses and parking garages

Complementary

Operating angle	90 °
Direction change type	Horizontal
Product destination	T-piece for KG281 cable tray 60 mm height and 330 mm width
Fixing mode	Screwless
Material with surface treatment	Steel, pre-galvanized
Corrosion class	C2
Length	430 mm
Height	11 mm
Width	530 mm
Product weight	1.398 kg / set of 100

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1101 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications