



Main

Range of product	Stago
Product or component type	Bend

Complementary

Operating angle	90 °
Direction change type	Horizontal
Inner radius	100 mm
Adjustment	Foldable
Product destination	KG281 cable tray 60 mm height and 400 mm width
Fixing mode	By screw
Material with surface treatment	Steel, pre-galvanized (RAL 1013)
Corrosion class	C2
Height	60 mm
Width	520 mm
Depth	520 mm
Product weight	2.242 kg / set of 1

Environment

Mounting location	For partly outdoor environment with low exposure to corrosion, such as ware-houses and parking garages
-------------------	--

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1101 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications