



Main

Product or component type	Branching piece
---------------------------	-----------------

Complementary

Operating angle	90 °
Direction change type	Horizontal
Adjustment	Foldable
Product destination	KG281 cable tray 60 mm height and 600 mm depth
Fixing mode	Screwless
Material	Steel with pre-galvanized RAL 1013
Height	60 mm
Width	840 mm
Depth	140 mm
Inner radius	100 mm

Environment

Atmospheric-corrosivity category	C2
Environmental characteristic	Partly outdoor environment with low exposure to corrosion ware-houses and parking garages
Product weight	0.83 kg set of 1