

Product data sheet

Specifications



Stago - t-piece flat 60x250mm pre-galvanized RAL1013

CSU36152512

⚠ Discontinued on: Sep 30, 2020

⚠ End-of-service on: Oct 26, 2020

⚠ Discontinued

Main

Product Or Component Type	T-piece
---------------------------	---------

Complementary

Operating Angle	90 °
Direction Change Type	Horizontal
Adjustment	Foldable
Product Destination	Cable tray KG281 H= 60 mm W= 250 mm
Fixing Mode	Screwless
Material	Steel pre-galvanized, RAL 1013
Inner Radius	100 mm
Height	14 mm
Width	631 mm
Depth	497 mm

Environment

Atmospheric-Corrosivity Category	C2
Environmental Characteristic	Partly outdoor environment with low exposure to corrosion ware-houses and parking garages

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications