


Product data sheet

Specifications



Stago - t-piece formed 60x250mm hot-dip galvanised

CSU361525124

 **Discontinued on:** Sep 27, 2019

 **Discontinued**

Main

| | |
|---------------------------|---------|
| Product Or Component Type | T-piece |
|---------------------------|---------|

Complementary

| | |
|-----------------------|-------------------------------------|
| Operating Angle | 90 ° |
| Direction Change Type | Vertical |
| Adjustment | Fixed |
| Product Destination | Cable tray KB184 H= 60 mm W= 250 mm |
| Fixing Mode | Screwless |
| Material | Steel hot-dip galvanized |
| Inner Radius | 100 mm |
| Height | 63 mm |
| Width | 656 mm |
| Depth | 455 mm |

Environment

| | |
|----------------------------------|--|
| Atmospheric-Corrosivity Category | C3/C4 |
| Environmental Characteristic | Area with high level of environmental corrosion, humidity and airborne pollution industrial and coastal areas, chemical plants |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications