

Product data sheet

Specifications



Stago - t-piece flat 60x600mm pre-galvanized RAL1013

CSU36156012

 **Discontinued on:** Sep 19, 2018

 **Discontinued**

Main

Product Or Component Type	T-piece
---------------------------	---------

Complementary

Operating Angle	90 °
Direction Change Type	Horizontal
Adjustment	Foldable
Product Destination	Cable tray KG281 H= 60 mm W= 600 mm
Fixing Mode	Screwless
Material	Steel pre-galvanized, RAL 1013
Inner Radius	100 mm
Height	60 mm
Width	840 mm
Depth	720 mm

Environment

Atmospheric-Corrosivity Category	C2
Environmental Characteristic	Partly outdoor environment with low exposure to corrosion ware-houses and parking garages

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications