



Main

Product or component type	T-piece
---------------------------	---------

Complementary

Operating angle	90 °
Direction change type	Vertical
Adjustment	Foldable
Product destination	Cable tray KG281 height 60 mm width 500 mm
Fixing mode	Screwless
Material	Steel with pre-galvanized RAL 1013
Inner radius	100 mm

Environment

Atmospheric-corrosivity category	C2
Environmental characteristic	Partly outdoor environment with low exposure to corrosion ware-houses and parking garages

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications