

Product data sheet

Characteristics

CSU36223372

Stago - external riser flat - 60x330 mm - steel - pre-galvanized - RAL9010



Main

Range of product	Stago
Range	Stago
Product or component type	Riser

Complementary

Operating angle	90 °
Direction change type	Vertical
Inner radius	120 mm
Adjustment	Foldable
Product destination	KG281 cable tray 60 mm height and 330 mm width
Fixing mode	Screwless
Corrosion class	C2
Thickness	1 mm
Product weight	0.761 kg / set of 100

Environment

Mounting location	For partly outdoor environment with low exposure to corrosion, such as ware-houses and parking garages
-------------------	--

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1101 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations