

Product data sheet

Characteristics

CSU36230712

Stago - internal riser flat - 60x70 mm - steel - pre-galvanized - RAL1013



Main

Range of product	Stago
Range	Stago
Product or component type	Riser
Device application	Cable management

Complementary

Operating angle	90 °
Direction change type	Vertical
Inner radius	180 mm
Adjustment	Foldable
Shape	Bended
Product destination	KG281 cable tray 60 mm height and 70 mm width
Fixing mode	Screwless
Material with surface treatment	Steel, pre-galvanized (RAL 1013)
Corrosion class	C2
Thickness	1 mm
Height	14 mm
Width	287 mm
Depth	270 mm
Product weight	0.309 kg / set of 1

Environment

Mounting location	For partly outdoor environment with low exposure to corrosion, such as ware-houses and parking garages
-------------------	--

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1101 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications