



Main

Range of product	Performa
Product or component type	Mesh tray
Quantity per set	6 m

Complementary

Shape	U-shape
Material	Steel C4D, zinc+
Atmospheric-corrosivity category	C3/C4
Longitudinal wire diameter	4.9 mm
Transversal wire diameter	3.9 mm
Cable cross section	12328 mm ²
Standards	EN/ISO 9227 DIN 4102-12 IEC 61537 EN 10244-2 IEC 60068-2-75 EN 50102
Length	3 m
Height	75 mm
Width	200 mm
Height compatibility	70 mm
Width compatibility	200 mm
Surface treatment compatibility	Zinc+

Environment

Ambient air temperature for operation	-40...120 °C
IK degree of protection	IK10
Fire resistance	960 °C, for 90 min according to DIN 4102-12 for classification E90

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications