



Main

Range of product	Stago
Product or component type	Cover
Mounting location	For area with almost permanent high levels of humidity and airborne pollution, such as tunnels and dockyards

Complementary

Operating angle	90 °
Direction change type	Horizontal
Product destination	T-piece for ES114 cable tray 60 mm height and 500 mm width T-piece for ES114 cable tray 110 mm height and 500 mm width
Fixing mode	Screwless
Material with surface treatment	Stainless steel AISI 304
Corrosion class	C5-I
Product weight	4.65 kg / set of 100