


# Product data sheet

Specifications



## Stago - external riser formed - 60x120 mm - stainless steel AISI 316

CSU70651240

 **Discontinued on:** Sep 19, 2018

 **Discontinued**

### Main

|                           |       |
|---------------------------|-------|
| Range Of Product          | Stago |
| Range                     | Stago |
| Product Or Component Type | Riser |

### Complementary

|                       |                                     |
|-----------------------|-------------------------------------|
| Operating Angle       | 90 °                                |
| Direction Change Type | Vertical                            |
| Inner Radius          | 120 mm                              |
| Adjustment            | Fixed                               |
| Product Destination   | Cable tray ES114 H= 60 mm W= 120 mm |
| Fixing Mode           | By screw                            |
| Material              | Stainless steel AISI 316            |
| Corrosion Class       | C5-M                                |
| Height                | 300 mm                              |
| Width                 | 123 mm                              |
| Depth                 | 300 mm                              |

### Environment

|                   |   |
|-------------------|---|
| Mounting Location | Area with almost permanent high levels of humidity, airborne pollution and salt purifying plants and offshore |
|-------------------|---|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications