



Main

Range of product	Stago
Product or component type	Riser

Complementary

Operating angle	90 °
Direction change type	Vertical
Inner radius	180 mm
Adjustment	Fixed
Product destination	ES114 cable tray 110 mm height and 400 mm width
Fixing mode	By screw
Material with surface treatment	Stainless steel AISI 304
Corrosion class	C5-I

Environment

Mounting location	For area with almost permanent high levels of humidity and airborne pollution, such as tunnels and dockyards
-------------------	--

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications