



Main

| | |
|---------------------------|---|
| Range of product | Stago |
| Product or component type | Cable ladder |
| Device short name | WHS |
| Cable support type | High side |
| Mounting location | For area with high level of environmental corrosion, humidity and airborne pollution, such as industrial and coastal areas, chemical plants |

Complementary

| | |
|---------------------------------|---------------------------|
| Type of rung | C-profile |
| Fixation rung | Welded |
| Rung dual spacing | 250 mm |
| Fixing mode | By screw |
| Material with surface treatment | Steel, hot-dip galvanized |
| Corrosion class | C3/C4 |
| Thickness | 1.5 mm |
| Perforation location | Side perforation |
| Height | 60 mm |
| Width | 200 mm |
| Length | 3000 mm |
| Product weight | 3.23 kg / 100 m |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications