



has not been replaced. Please contact your customer care center for more information.

## Main

Range of product	Stago
Product or component type	X-junction
Cable support type	High side
Mounting location	Area with high level of environmental corrosion, humidity and airborne pollution industrial and coastal areas, chemical plants

## Complementary

Operating angle	90 °
Direction change type	Horizontal
Product destination	Cable ladder LB4000 H= 60 mm W= 400 mm Cable ladder WHS H= 60 mm W= 400 mm
Type of rung	C-profile
Fixation rung	Welded
Mounting mode	Push-in
Fixing mode	Screws By joint screwless
Material with surface treatment	Steel hot-dip galvanized
Corrosion class	C3/C4
Perforation location	Side perforation
Height	60 mm
Width	1500 mm
Depth	1500 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications