



Main

Range of product	Stago
Product or component type	X-junction
Cable support type	High side
Mounting location	For area with high level of environmental corrosion, humidity and airborne pollution, such as industrial and coastal areas, chemical plants

Complementary

Operating angle	90 °
Direction change type	Horizontal
Product destination	LB4000 cable ladder 60 mm height and 500 mm width WHS cable ladder 60 mm height and 500 mm width
Type of rung	C-profile
Fixation rung	Welded
Mounting mode	Push-in
Fixing mode	Screws By joint screwless
Material with surface treatment	Steel, hot-dip galvanized
Corrosion class	C3/C4
Perforation location	Side perforation
Height	60 mm
Width	1600 mm
Depth	1600 mm