



### Main

Range of product	Stago
Product or component type	Cable ladder
Device short name	WHS
Cable support type	High side
Mounting location	Area with high level of environmental corrosion, humidity and airborne pollution industrial and coastal areas, chemical plants

### Complementary

Type of side joist	Open profile
Type of rung	Perforated profile
Fixation rung	Welded
Rung dual spacing	250 mm
Fixing mode	By screw
Material with surface treatment	Steel hot-dip galvanized
Corrosion class	C3/C4
Thickness	1.5 mm
Perforation location	Side perforation
Height	100 mm
Width	200 mm
Length	3000 mm
Net weight	4.233 kg / 100 m

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope

Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations