



Main

Range of product	Stago
Product or component type	Bend
Cable support type	High side
Mounting location	For area with high level of environmental corrosion, humidity and airborne pollution, such as industrial and coastal areas, chemical plants

Complementary

Operating angle	90 °
Direction change type	Horizontal
Product destination	Cable ladder WHS 100 mm height and 200 mm width
Type of rung	C-profile
Fixation rung	Welded
Fixing mode	By screw
Material with surface treatment	Steel, hot-dip galvanized
Corrosion class	C3/C4
Perforation location	Side perforation
Height	100 mm
Width	200 mm
Product weight	2.4 kg / set of 1

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1833 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available

