



Main

Range of product	Stago
Product or component type	T-piece
Cable support type	High side
Mounting location	For area with high level of environmental corrosion, humidity and airborne pollution, such as industrial and coastal areas, chemical plants

Complementary

Operating angle	90 °
Direction change type	Horizontal
Product destination	WHS cable ladder 100 mm height and 800 mm width
Type of rung	C-profile
Fixation rung	Welded
Mounting mode	Push-in
Fixing mode	By nut
Material with surface treatment	Steel, hot-dip galvanized
Corrosion class	C3/C4
Perforation location	Side perforation
Height	100 mm
Width	800 mm
Product weight	12.075 kg / set of 100

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications