



Main

Range of product	Stago
Product or component type	Cable ladder
Device short name	LB4000
Cable support type	High side
Mounting location	Partly outdoor environment with low exposure to corrosion ware-houses and parking garages

Complementary

Type of side joist	Open profile
Type of rung	Perforated profile
Fixation rung	Welded
Rung dual spacing	100 mm
Fixing mode	By screw
Material with surface treatment	Steel pre-galvanized
Corrosion class	C2
Thickness	1 mm
Perforation location	Side perforation
Height	60 mm
Width	600 mm
Length	3000 mm
Net weight	4.65 kg / 100 m

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations