



Main

| | |
|---------------------------|---|
| Range of product | Stago |
| Product or component type | Cable ladder |
| Device short name | LB4000 |
| Cable support type | High side |
| Mounting location | Partly outdoor environment with low exposure to corrosion ware-houses and parking garages |

Complementary

| | |
|---------------------------------|----------------------|
| Type of rung | C-profile |
| Fixation rung | Welded |
| Rung dual spacing | 100 mm |
| Fixing mode | By screw |
| Material with surface treatment | Steel pre-galvanized |
| Corrosion class | C2 |
| Thickness | 1 mm |
| Perforation location | Side perforation |
| Height | 100 mm |
| Width | 200 mm |
| Length | 3000 mm |
| Net weight | 3.257 kg / 100 m |

Offer Sustainability

| | |
|--------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Not applicable, out of EU RoHS legal scope |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |

| | |
|----------------------------|---|
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |