



Main

Range of product	Stago
Product or component type	Bend
Cable support type	High side
Mounting location	Partly outdoor environment with low exposure to corrosion ware-houses and parking garages

Complementary

Operating angle	45 °
Direction change type	Horizontal
Product destination	Cable ladder LB4000 H= 60 mm W= 200 mm
Type of rung	C-profile
Fixation rung	Welded
Fixing mode	By screw
Material with surface treatment	Steel pre-galvanized
Corrosion class	C2
Perforation location	Side perforation
Height	60 mm
Width	750 mm
Depth	450 mm
Net weight	1.905 kg / set of 1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations