

Product data sheet

Specifications



Stago - horizontal bend 45° H15100 - 100x200 mm - steel - pre-galvanized

CSU737906

⚠ Discontinued on: Jan 3, 2022

⚠ Discontinued

Important message: This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link www.wibe-group.com for further details.

Main

Range Of Product	Stago
Product Or Component Type	Bend
Cable Support Type	High side
Mounting Location	Partly outdoor environment with low exposure to corrosion ware-houses and parking garages

Complementary

Operating Angle	45 °
Direction Change Type	Horizontal
Product Destination	Cable ladder LB4000 H= 100 mm W= 200 mm
Type Of Rung	C-profile
Fixation Rung	Welded
Fixing Mode	By screw
Material With Surface Treatment	Steel pre-galvanized
Corrosion Class	C2
Perforation Location	Side perforation
Height	100 mm
Width	750 mm
Depth	750 mm
Net Weight	2.105 kg / set of 1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10 cm
Package 1 Width	46.5 cm
Package 1 Length	78.1 cm
Package 1 Weight	2.105 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

