



Main

Range of product	Stago
Product or component type	Bend
Cable support type	High side
Mounting location	For partly outdoor environment with low exposure to corrosion, such as ware-houses and parking garages

Complementary

Operating angle	45 °
Direction change type	Horizontal
Product destination	Cable ladder LB4000 100 mm height and 600 mm width
Type of rung	C-profile
Fixation rung	Welded
Fixing mode	By screw
Material with surface treatment	Steel, pre-galvanized
Corrosion class	C2
Perforation location	Side perforation
Height	100 mm
Width	1150 mm
Depth	1150 mm
Product weight	4.405 kg / set of 1

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1101 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
