

Product data sheet

Specifications



Stago - cross piece H17 - 60x300 mm - steel - hot-dip galvanized

CSU737932

 **Discontinued on:** Dec 11, 2019

 **Discontinued**

Main

Range Of Product	Stago
Product Or Component Type	X-junction
Cable Support Type	High side
Mounting Location	Area with high level of environmental corrosion, humidity and airborne pollution industrial and coastal areas, chemical plants

Complementary

Operating Angle	90 °
Direction Change Type	Horizontal
Product Destination	Cable ladder LB4000 H= 60 mm W= 300 mm Cable ladder WHS H= 60 mm W= 300 mm
Type Of Rung	C-profile
Fixation Rung	Welded
Mounting Mode	Push-in
Fixing Mode	Screws By joint screwless
Material With Surface Treatment	Steel hot-dip galvanized
Corrosion Class	C3/C4
Perforation Location	Side perforation
Height	60 mm
Width	1400 mm
Depth	1400 mm
Net Weight	7.11 kg / set of 1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	29.9 cm
Package 1 Width	145 cm
Package 1 Length	145 cm
Package 1 Weight	7.1 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications