



### Main

Range of product	Stago
Product or component type	Fibre optic duct
Mounting location	Partly outdoor environment with low exposure to corrosion white space - data center

### Complementary

Product destination	cable duct
Fixing mode	Screwless By bolt and nut
Material with surface treatment	Steel, pre-galvanized, powder coated RAL 1023
Height	60 mm
Width	300 mm
Length	3000 mm

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications