

Product data sheet

Specifications



Stago - hinge coupler - 60 mm - stainless steel AISI 304

CSU76120030

 **Discontinued on:** Jan 3, 2022

 **Discontinued**

Important message: This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link www.wibe-group.com for further details.

Main

Range Of Product	Stago
Product Or Component Type	Hinge coupler
Mounting Location	Area with almost permanent high levels of humidity and airborne pollution tunnels and dockyards

Complementary

Operating Angle	0...180 °
Direction Change Type	Vertical
Product Destination	Cable tray ES114 H= 60 mm W= 70 mm Cable tray ES114 H= 60 mm W= 100 mm Cable tray ES114 H= 60 mm W= 120 mm Cable tray ES114 H= 60 mm W= 150 mm Cable tray ES114 H= 60 mm W= 200 mm Cable tray ES114 H= 60 mm W= 250 mm Cable tray ES114 H= 60 mm W= 300 mm Cable tray ES114 H= 60 mm W= 330 mm
Fixing Mode	By screw
Material With Surface Treatment	Stainless steel AISI 304
Corrosion Class	C5-I
Height	57 mm
Width	250 mm
Length	11 mm
Net Weight	0.22 kg / set of 1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.1 cm
Package 1 Width	5.7 cm
Package 1 Length	25 cm
Package 1 Weight	370 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations