

Product data sheet

Specifications



Stago - hinge coupler - 60 mm - stainless steel AISI 316

CSU76120040

⚠ Discontinued on: Sep 19, 2018

⚠ Discontinued

Main

Range Of Product	Stago
Product Or Component Type	Hinge coupler
Mounting Location	Area with almost permanent high levels of humidity, airborne pollution and salt purifying plants and offshore

Complementary

Operating Angle	0...180 °
Direction Change Type	Vertical
Product Destination	Cable tray ES114 H= 60 mm
Fixing Mode	By screw
Material With Surface Treatment	Stainless steel AISI 316
Corrosion Class	C5-M
Height	57 mm
Width	250 mm
Length	11 mm
Net Weight	0.511 kg / set of 1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications